

Garant
GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank \varnothing / insert size: 20/11mm

Order data

Order number	261319 20/11
GTIN	4062406711139
Item class	21T

Technical description

Clamping height L_2	18 mm
Series	GARANT Master
suitable indexable insert	VC.. 1103..
Insert size	11 mm
ISO code toolholder	A20R SVUCR/L11
Head length L_1	36 mm
Overall length L	200 mm
Shank $\varnothing D_s$	20 mm
Centre offset L_3	13 mm
Pack of insert screws	269028 7
Setting angle κ	93 degrees
Minimum pre-drill $\varnothing D_{min}$	24 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar