

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank \varnothing / insert size: 16/11mm

Order data

Order number	261318 16/11
GTIN	4062406711313
Item class	21T

Technical description

Overall length L	180 mm
Shank \varnothing D _s	16 mm
Setting angle κ	93 degrees
suitable indexable insert	VC.. 1103..
Clamping height L ₂	15 mm
Head length L ₁	31 mm
ISO code toolholder	A16Q SVUCR/L11
Minimum pre-drill \varnothing D _{min}	20 mm
Pack of insert screws	269028 7
Insert size	11 mm
Centre offset L ₃	11 mm
Series	GARANT Master
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar