

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank \varnothing / insert size: 25/16mm

Order data

Order number	261318 25/16
GTIN	4062406711337
Item class	21T

Technical description

Overall length L	200 mm
Shank \varnothing D _s	25 mm
Insert size	16 mm
Centre offset L ₃	17 mm
ISO code toolholder	A25R SVUCR/L16
Setting angle κ	93 degrees
suitable indexable insert	VC.. 1604..
Series	GARANT Master
Head length L ₁	40 mm
Pack of insert screws	269028 8
Minimum pre-drill \varnothing D _{min}	31 mm
Clamping height L ₂	23 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar