

Garant**Digital dial indicator 0.01 mm reading, Measuring range: 25mm****Order data**

Order number	434330 25
GTIN	4062406720124
Item class	41C

Description**Version:**

Digital dial indicator with sturdy aluminium casing and **very large** display with integral three-colour tolerance LEDs. Power-saving mode and automatic wake-up, **absolute system**. Min./max./delta, tolerance, conversion factor, auto-off. Preset any value. Reversible direction of measurement.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948, lifting lever No. 434212, spare and special contact points No. 434900; 434910, battery pack No. 404310.

Technical description

Clamping shank \varnothing h6	8 mm
Reversible reading	0.0005 in

Article no of the battery / rechargeable battery fitted	081560 CR2032
Measuring range	0 - 25 mm
Battery type	Button cell
IP Index of Protection	IP 54
Gauging force	0.65 – 1.15 N
Calibration	C1
Number of batteries contained	1
Body Ø	59.5 mm
Power supply	Battery-powered
Reversible reading	0.01 mm
Thickness of housing	32.9 mm
Measurement variation E MPE (measurement range)	0.01 mm
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	USB interface
Interface	Digimatic interface
Preset function	yes
Measurement technology	digital
Material of the housing	Aluminium
Type of product	dial gauge

Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm	023000 30
DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 100 mm	023010 100

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------