

Garant
Digital dial indicator 0.001 mm reading, Measuring range: 25

Order data

| | |
|--------------|---------------|
| Order number | 434334 25 |
| GTIN | 4062406720148 |
| Item class | 41C |

Description
Version:

Digital dial indicator with sturdy aluminium casing and **very large** display with integral three-colour tolerance LEDs. Power-saving mode and automatic wake-up, **absolute system**. Min./max./delta, tolerance, conversion factor, auto-off. Preset any value. Reversible direction of measurement.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948, lifting lever No. 434212, spare and special contact points No. 434900; 434910, battery pack No. 404310.

Technical description

| | |
|---------------------------------|---------------|
| Gauging force | 0.65 – 1.15 N |
| Clamping shank \varnothing h6 | 8 mm |

| | |
|---|-------------------------|
| Battery type | Button cell |
| Calibration | C1 |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032 |
| Measuring range | 0 - 25 mm |
| Reversible reading | 0.00005 in |
| Power supply | Battery-powered |
| Number of batteries contained | 1 |
| IP Index of Protection | IP 54 |
| Body Ø | 59.5 mm |
| Reversible reading | 0.001 mm |
| Thickness of housing | 32.9 mm |
| Measurement variation E MPE (measurement range) | 0.004 mm |
| Standard | Manufacturer's standard |
| Reversible reading | mm / inch |
| Interface | USB interface |
| Interface | Digimatic interface |
| Preset function | yes |
| Measurement technology | digital |
| Material of the housing | Aluminium |
| Type of product | dial gauge |

Services

| | |
|--|------------|
| CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm | 023000 30 |
| DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 100 mm | 023010 100 |

Accessories

| | |
|---|---------------|
| Button cell / special battery Battery type CR2032 | 081560 CR2032 |
|---|---------------|