

**Garant****Digital dial indicator 0.01 mm reading, Measuring range: 12,5mm****Order data**

Order number	434330 12,5
GTIN	4062406720117
Item class	41C

**Description****Version:**

Digital dial indicator with sturdy aluminium casing and **very large** display with integral three-colour tolerance LEDs. Power-saving mode and automatic wake-up, **absolute system**. Min./max./delta, tolerance, conversion factor, auto-off. Preset any value. Reversible direction of measurement.

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size CR2032.

**Optional extras:**

Data cable No. 498948, lifting lever No. 434212, spare and special contact points No. 434900; 434910, battery pack No. 404310.

**Technical description**

Thickness of housing	32.9 mm
Calibration	C1

Reversible reading	0.01 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Clamping shank $\varnothing$ h6	8 mm
Body $\varnothing$	59.5 mm
Battery type	Button cell
IP Index of Protection	IP 54
Gauging force	0.65 – 0.90 N
Reversible reading	0.0005 in
Measuring range	0 - 12.5 mm
Number of batteries contained	1
Power supply	Battery-powered
Measurement variation E MPE (measurement range)	0.01 mm
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	USB interface
Interface	Digimatic interface
Preset function	yes
Measurement technology	digital
Material of the housing	Aluminium
Type of product	dial gauge

## Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023000 12,5
DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------