



PU coiled hose 1/4 inch with eSafe steel safety coupling Ø 8 × 12 mm, usable hose length: 6m



Order data

Order number	080248 6
GTIN	7391390141897
Item class	08A

Description

Version:

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant between - 20/+ 60°C. Maximum operating pressure 16 bar. Complies with ISO standard B.

Note:

The CEJN series 310 is suitable for the markets of Benelux, France, North America and Norway.

Technical description

Hose internal Ø	8 mm
maximum bursting pressure	35 bar
Connection quick-release coupling	1/4 in
Hose external Ø	12 mm
usable hose length	6 m
Material	PU spiral hose
Connection plug nipple	1/4 in
maximum operating pressure	10 bar
Colour	blue

Type of product

Hose

AccessoriesCoupling adaptor with external threadSet of 5 Connection
external thread 1/4 in

080300 1/4

Safety couplingExternal thread Connection external thread
1/4 in

080276 1/4