



## PU coiled hose 1/4 inch with eSafe steel safety coupling Ø 8 × 12 mm, usable hose length: 2m



### Order data

Order number	080248 2
GTIN	7391390275448
Item class	08A

### Description

#### Version:

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant between - 20/+ 60°C. Maximum operating pressure 16 bar. Complies with ISO standard B.

#### Note:

The CEJN series 310 is suitable for the markets of Benelux, France, North America and Norway.

### Technical description

usable hose length	2 m
Colour	blue
maximum bursting pressure	35 bar
maximum operating pressure	10 bar
Connection plug nipple	1/4 in
Hose internal Ø	8 mm
Connection quick-release coupling	1/4 in
Hose external Ø	12 mm

Material	PU spiral hose
Type of product	Hose

---

## Accessories

Coupling adaptor with external threadSet of 5 Connection external thread 1/4 in	080300 1/4
Safety couplingExternal thread Connection external thread 1/4 in	080276 1/4