



PU coiled hose 1/2 inch with eSafe steel safety coupling Ø 11 × 16 mm, usable hose length: 4m



Order data

Order number	080249 4
GTIN	7391390305435
Item class	08A

Description

Version:

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant between - 20/+ 60°C. Maximum operating pressure 16 bar. Complies with ISO standard B.

Note:

The CEJN series 310 is suitable for the markets of Benelux, France, North America and Norway.

Technical description

Material	PU spiral hose
Hose internal Ø	11 mm
usable hose length	4 m
Connection quick-release coupling	1/2 in
Hose external Ø	16 mm
Colour	blue

Connection plug nipple	1/2 in
maximum bursting pressure	35 bar
maximum operating pressure	10 bar
Type of product	Hose

Accessories

Safety coupling External thread Connection external thread 1/2 in	080276 1/2
--	------------