

**Manual changeover device for MANOK, Clamping head (SK): 80****Order data**

Order number	329832 80
GTIN	2050002069473
Item class	33H

Description**Version:**

Changeover device for manual clamping head change.

Application:

Versatile application, e.g. machining centres, measuring machines, pillar drills.

Note:

For suitable clamping heads see No.329910–329946.

Technical description

Arbor size	80 mm
Type of product	Changing device

Accessories

329944 46

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 46 mm

Clamping headsmooth Clamping Ø (1 mm increments) 29
mm

329940 29

Clamping headsmooth Clamping Ø (1 mm increments) 52
mm

329940 52

Clamping headsmooth Clamping Ø (1 mm increments) 77
mm

329940 77

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 32 mm

329944 32

Clamping headsmooth Clamping Ø (1 mm increments) 72
mm

329940 72

Clamping headsmooth Clamping Ø (1 mm increments) 14
mm

329940 14

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 71 mm

329944 71

Clamping headsmooth Clamping Ø (1 mm increments) 30
mm

329940 30

Clamping headsmooth Clamping Ø (1 mm increments) 28
mm

329940 28

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 29 mm

329944 29

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 12 mm

329944 12

Clamping headsmooth Clamping Ø (1 mm increments) 50
mm

329940 50

Clamping headsmooth Clamping Ø (1 mm increments) 10
mm

329940 10

Clamping headsmooth Clamping Ø (1 mm increments) 7
mm

329940 7

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 11 mm

329944 11

Clamping headsmooth Clamping Ø (1 mm increments) 36
mm

329940 36

329944 19

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 19 mm

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 47 mm

329944 47

Clamping headsmooth Clamping Ø (1 mm increments) 37
mm

329940 37

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 63 mm

329944 63

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 24 mm

329944 24

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 37 mm

329944 37

Clamping headsmooth Clamping Ø (1 mm increments) 20
mm

329940 20

Clamping headsmooth Clamping Ø (1 mm increments) 54
mm

329940 54

Clamping headsmooth Clamping Ø (1 mm increments) 51
mm

329940 51

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 62 mm

329944 62

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 23 mm

329944 23

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 64 mm

329944 64

Clamping headsmooth Clamping Ø (1 mm increments) 34
mm

329940 34

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 42 mm

329944 42

Clamping headsmooth Clamping Ø (1 mm increments) 65
mm

329940 65

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 30 mm

329944 30

Clamping headsmooth Clamping Ø (1 mm increments) 5
mm

329940 5

329944 13

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 13 mm

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 33 mm

329944 33

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 77 mm

329944 77

Clamping headsmooth Clamping Ø (1 mm increments) 16
mm

329940 16

Clamping headsoft Initial bore Ø 40 mm

329946 40

Clamping headsmooth Clamping Ø (1 mm increments) 71
mm

329940 71

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 55 mm

329944 55

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 56 mm

329944 56

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 72 mm

329944 72

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 34 mm

329944 34

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 57 mm

329944 57

Clamping headsmooth Clamping Ø (1 mm increments) 48
mm

329940 48

Clamping headsmooth Clamping Ø (1 mm increments) 39
mm

329940 39

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 14 mm

329944 14

Clamping headsmooth Clamping Ø (1 mm increments) 41
mm

329940 41

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 27 mm

329944 27

Clamping headwith transverse and longitudinal serrations.
Clamping Ø (1 mm increments) 70 mm

329944 70

Clamping headsmooth Clamping Ø (1 mm increments) 78
mm

329940 78

Clamping headsmooth Clamping Ø (1 mm increments) 19 mm	329940 19
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 67 mm	329944 67
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 22 mm	329944 22
Clamping headsmooth Clamping Ø (1 mm increments) 64 mm	329940 64
Clamping headsmooth Clamping Ø (1 mm increments) 75 mm	329940 75
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 74 mm	329944 74
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 76 mm	329944 76
Clamping headsmooth Clamping Ø (1 mm increments) 66 mm	329940 66
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 52 mm	329944 52
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 35 mm	329944 35
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 79 mm	329944 79
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 25 mm	329944 25
Clamping headsoft Initial bore Ø 8 mm	329946 8
Clamping headsmooth Clamping Ø (1 mm increments) 47 mm	329940 47
Clamping headsmooth Clamping Ø (1 mm increments) 32 mm	329940 32
Clamping headsmooth Clamping Ø (1 mm increments) 62 mm	329940 62
Clamping headsmooth Clamping Ø (1 mm increments) 23 mm	329940 23
Clamping headsmooth Clamping Ø (1 mm increments) 69 mm	329940 69

Clamping headsmooth Clamping Ø (1 mm increments) 61 mm	329940 61
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 26 mm	329944 26
Clamping headsmooth Clamping Ø (1 mm increments) 13 mm	329940 13
Clamping headsmooth Clamping Ø (1 mm increments) 33 mm	329940 33
Clamping headsoft Initial bore Ø 60 mm	329946 60
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 61 mm	329944 61
Clamping headsmooth Clamping Ø (1 mm increments) 22 mm	329940 22
Clamping headsmooth Clamping Ø (1 mm increments) 43 mm	329940 43
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 51 mm	329944 51
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 78 mm	329944 78
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 48 mm	329944 48
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 75 mm	329944 75
Clamping headsmooth Clamping Ø (1 mm increments) 67 mm	329940 67
Clamping headsmooth Clamping Ø (1 mm increments) 44 mm	329940 44
Clamping headsmooth Clamping Ø (1 mm increments) 17 mm	329940 17
Clamping headsmooth Clamping Ø (1 mm increments) 53 mm	329940 53
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 80 mm	329944 80
Clamping headsmooth Clamping Ø (1 mm increments) 59 mm	329940 59

Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 28 mm	329944 28
Clamping headsmooth Clamping Ø (1 mm increments) 18 mm	329940 18
Clamping headsmooth Clamping Ø (1 mm increments) 26 mm	329940 26
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 49 mm	329944 49
Clamping headsmooth Clamping Ø (1 mm increments) 11 mm	329940 11
Clamping headsmooth Clamping Ø (1 mm increments) 40 mm	329940 40
Clamping headsmooth Clamping Ø (1 mm increments) 68 mm	329940 68
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 31 mm	329944 31
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 66 mm	329944 66
Clamping headsmooth Clamping Ø (1 mm increments) 42 mm	329940 42
Clamping headsmooth Clamping Ø (1 mm increments) 76 mm	329940 76
Clamping headsoft Initial bore Ø 20 mm	329946 20
Clamping headsmooth Clamping Ø (1 mm increments) 6 mm	329940 6
Clamping headsmooth Clamping Ø (1 mm increments) 8 mm	329940 8
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 54 mm	329944 54
Clamping headsmooth Clamping Ø (1 mm increments) 73 mm	329940 73
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 58 mm	329944 58
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 43 mm	329944 43

Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 44 mm	329944 44
Clamping headsmooth Clamping Ø (1 mm increments) 49 mm	329940 49
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 36 mm	329944 36
Clamping headsmooth Clamping Ø (1 mm increments) 31 mm	329940 31
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 16 mm	329944 16
Clamping headsmooth Clamping Ø (1 mm increments) 12 mm	329940 12
Clamping headsmooth Clamping Ø (1 mm increments) 63 mm	329940 63
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 65 mm	329944 65
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 50 mm	329944 50
Clamping headsmooth Clamping Ø (1 mm increments) 45 mm	329940 45
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 15 mm	329944 15
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 17 mm	329944 17
Clamping headsmooth Clamping Ø (1 mm increments) 27 mm	329940 27
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 38 mm	329944 38
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 60 mm	329944 60
Clamping headsmooth Clamping Ø (1 mm increments) 35 mm	329940 35
Clamping headsmooth Clamping Ø (1 mm increments) 21 mm	329940 21
	329940 79

Clamping headsmooth Clamping \varnothing (1 mm increments) 79 mm

Clamping headwith transverse and longitudinal serrations.
Clamping \varnothing (1 mm increments) 53 mm

329944 53

Clamping headsmooth Clamping \varnothing (1 mm increments) 46 mm

329940 46

Clamping headwith transverse and longitudinal serrations.
Clamping \varnothing (1 mm increments) 21 mm

329944 21

Clamping headwith transverse and longitudinal serrations.
Clamping \varnothing (1 mm increments) 68 mm

329944 68

Clamping headsmooth Clamping \varnothing (1 mm increments) 70 mm

329940 70

Clamping headsmooth Clamping \varnothing (1 mm increments) 57 mm

329940 57

Clamping headsmooth Clamping \varnothing (1 mm increments) 24 mm

329940 24

Clamping headsmooth Clamping \varnothing (1 mm increments) 25 mm

329940 25

Clamping headwith transverse and longitudinal serrations.
Clamping \varnothing (1 mm increments) 20 mm

329944 20

Clamping headwith transverse and longitudinal serrations.
Clamping \varnothing (1 mm increments) 40 mm

329944 40

Clamping headwith transverse and longitudinal serrations.
Clamping \varnothing (1 mm increments) 59 mm

329944 59

Clamping headsmooth Clamping \varnothing (1 mm increments) 74 mm

329940 74

Clamping headsmooth Clamping \varnothing (1 mm increments) 55 mm

329940 55

Clamping headsmooth Clamping \varnothing (1 mm increments) 15 mm

329940 15

Clamping headwith transverse and longitudinal serrations.
Clamping \varnothing (1 mm increments) 45 mm

329944 45

Clamping headwith transverse and longitudinal serrations.
Clamping \varnothing (1 mm increments) 41 mm

329944 41

329940 56

Clamping headsmooth Clamping Ø (1 mm increments) 56 mm	
Clamping headsmooth Clamping Ø (1 mm increments) 80 mm	329940 80
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 73 mm	329944 73
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 18 mm	329944 18
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 39 mm	329944 39
Clamping headwith transverse and longitudinal serrations. Clamping Ø (1 mm increments) 69 mm	329944 69
Clamping headsmooth Clamping Ø (1 mm increments) 38 mm	329940 38
Clamping headsmooth Clamping Ø (1 mm increments) 58 mm	329940 58
Clamping headsmooth Clamping Ø (1 mm increments) 60 mm	329940 60
Clamping headsmooth Clamping Ø (1 mm increments) 9 mm	329940 9