


Garant
GARANT Master eco lever lock toolholder short, left-hand, Shank / insert size: 20/12mm

Order data

Order number	250001 20/12
GTIN	4062406733261
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholder No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Lever	259015 15
ISO code toolholder	PCLNR/L 2020X12
Shim	259031 5
Functional width L ₄	25 mm
Insert size	12 mm
Head length L ₁	30 mm
Shank size	20 mm
Lever screw	259018 15
Overall length L	90 mm

Spring	259046 4
Series	Master Eco
suitable indexable insert	CN.. 1204..
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar