

Garant
GARANT Master eco lever lock toolholder short, right-hand, Shank / insert size: 20/15mm

Order data

| | |
|--------------|---------------|
| Order number | 250624 20/15 |
| GTIN | 4062406728946 |
| Item class | 21U |

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

| | |
|---------------------------------|-------------|
| Series | Master Eco |
| Head length L ₁ | 40 mm |
| Overall length L | 100 mm |
| Functional width L ₄ | 25 mm |
| Insert size | 15 mm |
| Lever | 259015 17 |
| Shim | 259031 45 |
| suitable indexable insert | DN.. 1506.. |
| Lever screw | 259018 17 |
| Spring | 259046 4 |

| | |
|------------------------|-------------------------------|
| Shank size | 20 mm |
| ISO code toolholder | PDJNR/L 2020H15 |
| Standard | DIN ISO 5610 |
| Application type | right-hand |
| Through-coolant | yes |
| Setting angle κ | 93 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |