

Garant
GARANT Master eco lever lock toolholder short, right-hand, Shank / insert size: 16/08mm

Order data

| | |
|--------------|---------------|
| Order number | 251910 16/08 |
| GTIN | 4062406733872 |
| Item class | 21U |

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

| | |
|---------------------------------|----------------|
| ISO code toolholder | PWLNRL 1620F08 |
| Shank size | 16 mm |
| Overall length L | 80 mm |
| Lever | 259015 15 |
| Shim | 259031 48 |
| Insert size | 8 mm |
| suitable indexable insert | WN.. 0804.. |
| Functional width L ₄ | 25 mm |
| Head length L ₁ | 30 mm |

| | |
|------------------------|-------------------------------|
| Lever screw | 259018 15 |
| Series | Master Eco |
| Spring | 259046 4 |
| Standard | Works standard |
| Application type | right-hand |
| Through-coolant | yes |
| Setting angle κ | 95 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | QuickTurn clamping toolholder |