

Garant
GARANT Master eco clamping toolholder short, right-hand, Shank / insert size: 20/16mm

Order data

Order number	251696 20/16
GTIN	4062406734626
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Series	Master Eco
Head length L ₁	40 mm
Overall length L	100 mm
Shim	259033 10
Shank size	20 mm
suitable indexable insert	VN.. 1604..
Screw for clamping claw	259021 7
Shim screw	259027 7
Clamping claw	259038 19

Functional width L ₄	25 mm
Insert size	16 mm
ISO code toolholder	MVJNR/L 2020H16
Standard	Works standard
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Clamping claw Type 19	259038 19
Shim Type 1	259031 1
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2
Screw for clamping claw Type 7	259021 7
Shim screw Type 9	259025 9
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500