

**Garant**
**GARANT Master eco clamping toolholder short, right-hand, Shank / insert size: 20/08mm**

**Order data**

Order number	251922 20/08
GTIN	4062406734664
Item class	21U

**Description**
**Version:**

Highly efficient cooling directly on the cutter and additional flank face cooling.

**Note:**

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

**Technical description**

Pin	259049 7
Series	Master Eco
Shim	259033 6
Clamping claw	259038 18
Head length L <sub>1</sub>	35 mm
Functional width L <sub>4</sub>	25 mm
Screw for clamping claw	259021 6
suitable indexable insert	WN.. 0804..
Shank size	20 mm

Insert size	8 mm
ISO code toolholder	MWLNR/L 2020X08
Overall length L	95 mm
Standard	Works standard
Application type	right-hand
Through-coolant	yes
Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	QuickTurn clamping toolholder