

Garant

GARANT Master eco screw-on toolholder screw clamping, right-hand, Shank size / insert size L: 16/16mm



Order data

Order number	271997 16/16
GTIN	4062406734718
Item class	21U

Description

Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Supplied with:

With shim 1.5°.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholder No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Clamping screw for shim	279824 1
Series	Master Eco
Functional width L ₄	20 mm
Shim 1.5°	279819 1
Overall length L	80 mm
Head length L ₁	30 mm
Shank size	16 mm
Insert screw for threading insert	269023 3
Insert size	16 mm

Application type	right-hand
Through-coolant	yes
Type of product	Boring bar