

## Garant

### GARANT Master eco screw-on toolholder screw clamping, right-hand, Shank size / insert size L: 20/16mm



#### Order data

Order number	271997 20/16
GTIN	4062406734725
Item class	21U

#### Description

##### Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

##### Supplied with:

With shim 1.5°.

##### Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholder No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

#### Technical description

Insert screw for threading insert	269023 3
Head length L <sub>1</sub>	30 mm
Shank size	20 mm
Overall length L	90 mm
Series	Master Eco
Functional width L <sub>4</sub>	25 mm
Shim 1.5°	279819 1
Clamping screw for shim	279824 1
Insert size	16 mm

Application type	right-hand
Through-coolant	yes
Type of product	Boring bar