

Garant
GARANT Master eco screw-on toolholder screw clamping, right-hand, Shank size / insert size L: 25/16mm

Order data

Order number	271997 25/16
GTIN	4062406734732
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Supplied with:

With shim 1.5°.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholder No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Series	Master Eco
Clamping screw for shim	279824 1
Shim 1.5°	279819 1
Functional width L ₄	32 mm
Overall length L	100 mm
Insert screw for threading insert	269023 3
Head length L ₁	30 mm
Shank size	25 mm
Insert size	16 mm

Application type	right-hand
Through-coolant	yes
Type of product	Boring bar