



HCT digital dial indicator 0.01 mm reading, Measuring range: 25mm



Order data

Order number	434008 25
GTIN	4062406735029
Item class	42C

Description

Version:

Digital dial indicator in compact design with high-contrast digital display.

- **Reversible direction of measurement.**
- **Very narrow casing.**

Version with Bluetooth 5.0. Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app. Available free of charge for Android and iOS. Can also be used via a Human Interface Device (HID).

USB-C interface for power supply.

Supplied with:

Supplied with an eye on the cover and 1 battery No. 081560 size CR2032.

Optional extras:

Spare and special contact points No. 434900; 434910; 434915.

Technical description

Nominal voltage	3 V
Measuring range	0 - 25 mm

Reversible reading	0.0005 in
Series	HCT
Clamping shank - Ø h7	8 mm
Gauging force	0.8 – 1.7 N
Wireless application	HCT Mobile App
Wireless application	HID (Human Interface Device)
Wireless application	HCT Windows app
Thickness of housing	26 mm
Calibration	C1
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Body Ø	58 mm
Battery type	Button cell
Reversible reading	0.01 mm
Measurement variation E MPE (measurement range)	0.035 mm
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	Bluetooth interface
Measurement technology	digital
Packaging	sturdy box
Type of product	dial gauge

Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm	023000 30
---	-----------

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------

