

**HCT digital dial indicator 0.01 mm reading, Measuring range: 12,5mm****Order data**

Order number	434008 12,5
GTIN	4062406735012
Item class	42C

**Description****Version:**

Digital dial indicator in compact design with high-contrast digital display.

- **Reversible direction of measurement.**
- **Very narrow casing.**

Version with Bluetooth 5.0. Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app. Available free of charge for Android and iOS. Can also be used via a Human Interface Device (HID).

USB-C interface for power supply.

**Supplied with:**

Supplied with an eye on the cover and 1 battery No. 081560 size CR2032.

**Optional extras:**

Spare and special contact points No. 434900; 434910; 434915.

**Technical description**

Thickness of housing	26 mm
Measuring range	0 - 12.5 mm

Battery type	Button cell
Reversible reading	0.0005 in
Reversible reading	0.01 mm
Calibration	C1
Clamping shank - Ø h7	8 mm
Series	HCT
Gauging force	0.8 – 1.4 N
Body Ø	58 mm
Power supply	Battery-powered
Number of batteries contained	1
Nominal voltage	3 V
Article no of the battery / rechargeable battery fitted	081560 CR2032
Wireless application	HCT Mobile App
Wireless application	HID (Human Interface Device)
Wireless application	HCT Windows app
Measurement variation E MPE (measurement range)	0.025 mm
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	Bluetooth interface
Measurement technology	digital
Packaging	sturdy box
Type of product	dial gauge

## Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023000 12,5
DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5

## Accessories

Button cell / special battery Battery type CR2032

081560 CR2032