

**Coiled 1/4 inch nylon hose, with coupling, usable hose length: 7,5m****Order data**

Order number	080057 7,5
GTIN	4062406734855
Item class	02A

Description**Version:**

Flexible nylon hose. Temperature-resistant from -60 / +60°C.

Supplied with:

Supplied with 1 piece each of brass quick-release coupling and coupling adaptor.

Technical description

usable hose length	7.5 m
maximum operating pressure	10 bar
Hose internal Ø	6 mm
Temperature range	-60 - 60 °C
Connection quick-release coupling	1/4 in
Hose external Ø	8 mm
Type of product	Hose

Accessories

Quick connectwith internal thread Connection internal
thread 1/4 in

080171 1/4