

**Coiled 1/4 inch nylon hose, with coupling, usable hose length: 5m****Order data**

Order number	080057 5
GTIN	4062406734848
Item class	02A

Description**Version:**

Flexible nylon hose. Temperature-resistant from -60 / +60°C.

Supplied with:

Supplied with 1 piece each of brass quick-release coupling and coupling adaptor.

Technical description

maximum operating pressure	10 bar
Connection quick-release coupling	1/4 in
Temperature range	-60 - 60 °C
Hose internal Ø	6 mm
Hose external Ø	8 mm
usable hose length	5 m
Type of product	Hose

Accessories

Quick connectwith internal thread Connection internal
thread 1/4 in

080171 1/4