

**Coiled 3/8 inch nylon hose, with coupling, usable hose length: 5m****Order data**

Order number	080058 5
GTIN	4067263151883
Item class	02A

Description**Version:**

Flexible nylon hose. Temperature-resistant from -60 / +60°C.

Supplied with:

Supplied with 1 piece each of brass quick-release coupling and coupling adaptor.

Technical description

Hose external Ø	12 mm
usable hose length	5 m
Hose internal Ø	9 mm
Connection quick-release coupling	3/8 in
maximum operating pressure	10 bar
Temperature range	-60 - 60 °C
Type of product	Hose

Accessories

Quick connectwith internal thread Connection internal
thread 3/8 in

080171 3/8