

Garant

Mechanical measuring stand (with magnetic base), Throat: 290mm



Order data

Order number	441600 290
GTIN	4062406735142
Item class	41D

Description

Version:

Mechanic measuring stand with central clamping – all joints are rigidly clamped by means of the central boring head. Clamping force can be steplessly adjusted. **Large rubberised handwheel** (Ø approx. 45 mm or approx. 55 mm) for easy tightening and releasing of the clamp. The dial indicator mounting on the jointed arm rotates 360°, can be twisted 180° and is suitable for dial indicators with shank Ø 6 and 8 mm or vee block. Connection thread for magnetic base M8, connection thread for jointed arm at the top M6.

Stand with magnetic base and **ergonomic rotary switch**. High performance ferrite magnet with ground contact faces on the back and ground Vee underneath for placing on shafts and cylindrical bodies. **Plastic enclosure** of the magnetic base for easy handling, enhanced shock protection and thermal insulation.

Supplied with:

Measuring stand with magnetic base No. 440620 size 1.

Optional extras:

Holder for measuring stand No. 442100 and 442104.

Technical description

Magnetic force	1000 N
Throat	290 mm
Length of jointed arm L ₂	110 mm
Connection thread	M8
Alignment of connecting thread	side
Length of jointed arm L ₁	130 mm
Type of product	measuring stand

Accessories

Magnetic base Type 1	440620 1
----------------------	----------