

SWISS TOOLS

## Boring bar shank vibration-damped, HSK-T, Shank $\varnothing$ / $\varnothing$ D - A dimension: 63/40-226mm



### Order data

Order number	320104 63/40-226
GTIN	2050002062924
Item class	36D

### Description

#### Version:

- For efficient turning.
- For left-hand and right-hand turning.

#### Advantage:

- **Productivity gain - thanks to suppression of vibration the cutting data can be significantly increased.**
- **Improved surface quality.**
- **Improved process reliability.**
- **Improved chip clearance.**

#### Application:

For mounting exchangeable cutting heads.

#### Note:

For suitable interchangeable heads see No. 264826 – 264827.

### Technical description

Overhang dimension A	226 mm
Shank $\varnothing$	63 mm
$\varnothing$ D	40 mm
Adapter	HSK-T
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Boring bar base body

