

SWISS TOOLS

Boring bar shank vibration-damped, HSK-T, Shank \varnothing / \varnothing D - A dimension: 63/32-186mm



Order data

Order number	320104 63/32-186
GTIN	2050002062917
Item class	36D

Description

Version:

- For efficient turning.
- For left-hand and right-hand turning.

Advantage:

- **Productivity gain - thanks to suppression of vibration the cutting data can be significantly increased.**
- **Improved surface quality.**
- **Improved process reliability.**
- **Improved chip clearance.**

Application:

For mounting exchangeable cutting heads.

Note:

For suitable interchangeable heads see No. 264826 – 264827.

Technical description

Shank \varnothing	63 mm
Overhang dimension A	186 mm
\varnothing D	32 mm
Adapter	HSK-T
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Boring bar base body

