

SWISS TOOLS

**Boring bar shank vibration-damped, PSC, Shank  $\varnothing$  /  $\varnothing$  D - A dimension:  
63/32-194mm****Order data**

Order number	320409 63/32-194
GTIN	2050002063020
Item class	36D

**Description****Version:**

- For efficient turning.
- For left-hand and right-hand turning.

**Advantage:**

- **Productivity gain - thanks to suppression of vibration the cutting data can be significantly increased.**
- **Improved surface quality.**
- **Improved process reliability.**
- **Improved chip clearance.**

**Application:**

For mounting exchangeable cutting heads.

**Note:**

For suitable interchangeable heads see No. 264826 – 264827.

**Technical description**

Shank $\varnothing$	63 mm
Overhang dimension A	194 mm
$\varnothing$ D	32 mm
Adapter	PSC
Arbor standard	ISO 26623-1
Through-coolant	yes

Type of product

Boring bar base body