

SWISS TOOLS

**Boring bar shank vibration-damped, PSC, Shank \varnothing / \varnothing D - A dimension:
63/25-167mm****Order data**

Order number	320409 63/25-167
GTIN	2050002063013
Item class	36D

Description**Version:**

- For efficient turning.
- For left-hand and right-hand turning.

Advantage:

- Productivity gain - thanks to suppression of vibration the cutting data can be significantly increased.
- Improved surface quality.
- Improved process reliability.
- Improved chip clearance.

Application:

For mounting exchangeable cutting heads.

Note:

For suitable interchangeable heads see No. 264826 – 264827.

Technical description

Shank \varnothing	63 mm
Overhang dimension A	167 mm
\varnothing D	25 mm
Adapter	PSC
Arbor standard	ISO 26623-1
Through-coolant	yes

Type of product

Boring bar base body