

SWISS TOOLS

## Screw-on toolholder right-hand, PSC, Shank Ø / insert size: 50/16HPmm



### Order data

Order number	320415 50/16HP
GTIN	2050002063051
Item class	36D

### Description

#### Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

### Technical description

suitable indexable insert	16E..
Axis tip distance f	35 mm
Overhang dimension A	60 mm
Shank Ø	50 mm
Insert size	16HP
Adapter	PSC
Application type	right-hand
Arbor standard	ISO 26623-1
Through-coolant	yes
Shank type	Hollow shank taper

Type of product

Boring bar