

SWISS TOOLS

**Boring bar left-hand, PSC, Shank Ø / insert size: 40/16HPmm****Order data**

Order number	320416 40/16HP
GTIN	2050002063075
Item class	36D

**Description****Note:**

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.  
PSC clamping stud on request.

**Technical description**

Shank Ø	40 mm
suitable indexable insert	16E..
Overhang dimension A	50 mm
Axis tip distance f	27 mm
Insert size	16HP
Adapter	PSC
Application type	left-hand
Arbor standard	ISO 26623-1
Through-coolant	yes
Shank type	Hollow shank taper

Type of product

Boring bar