

# uvex

## Lace-up boot, black/yellow uvex 1, S2, EU shoe size: 47



### Order data

Order number	092118 47
GTIN	4031101534893
Item class	04V

### Description

#### Version:

Sporty, especially lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.

- **Micro-velour uppers.**
- **Distance Mesh lining material.**
- **100% metal-free uvex xenova® toecap.**
- **PU sole with TPU inserts with the best damping characteristics.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Lace-up boot with soft padded collar and padded tongue.

#### Standard:

EN ISO 20345:2011 S2 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

electrostatic characteristic: EGB/ESD

Protection class: S2

Material of protective toe-cap: Composite

Standard: Inlay type-tested according to DGUV regulation 191

### Technical description

Protection class	S2
------------------	----

oil- and petrol-resistant sole	yes
Material inner lining	Distance Mesh
suitable for those with chrome allergy.	yes
removable footbed	yes
against water penetration and water absorption	yes
Standard	Inlay type-tested according to DGUV regulation 191
contains no metal or leather	yes
EU shoe size	47
Energy absorption in the heel area	yes
Slip resistance	yes
The entire shoe is waterproof	yes
Material of protective toe-cap	Composite
Colour	black / yellow
anti-static	yes
Material of outer sole	Polyurethane
Closure	Laces
Shoe type	Bootlaces
Uppers material	Hydrophobic high-tech micro-velour
Series	uvex 1
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety boots