

SWISS TOOLS

Screw-on toolholder right-hand, PSC, Shank \varnothing / insert size: 63/16HPmm



Order data

Order number	320420 63/16HP
GTIN	2050002063129
Item class	36D

Description

Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

Technical description

Axis tip distance f	45 mm
suitable indexable insert	16E..
Overhang dimension A	65 mm
Insert size	16HP
Shank \varnothing	63 mm
Adapter	PSC
Application type	right-hand
Arbor standard	ISO 26623-1
Through-coolant	yes
Shank type	Hollow shank taper

Type of product

Boring bar