

SWISS TOOLS

## Screw-on toolholder right-hand, PSC, Shank $\varnothing$ / insert size: 40/16HPmm



### Order data

Order number	320420 40/16HP
GTIN	2050002063105
Item class	36D

### Description

#### Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

### Technical description

Overhang dimension A	50 mm
Axis tip distance f	27 mm
suitable indexable insert	16E..
Shank $\varnothing$	40 mm
Insert size	16HP
Adapter	PSC
Application type	right-hand
Arbor standard	ISO 26623-1
Through-coolant	yes
Shank type	Hollow shank taper

Type of product

Boring bar