

**HOLEX CleverDrill HSS jobber drill, uncoated, Ø DC h8: 15mm****Order data**

Order number	113006 15
GTIN	4062406743246
Item class	12B

Description**Version:**

Sturdy drills for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

Recommendation:**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c.$$

Note:

Successor product to No. 113005.

Technical description

Standard	DIN 1897
Shank Ø D _s	15 mm
Flute length L _c	56 mm
Tolerance nominal Ø	h8
Number of cutting edges Z	2
Feed f in steel < 750 N/mm ²	0.16 mm/rev.
Point angle	118 degrees
recommended maximum drilling depth L ₂	33.5 mm
Overall length L	111 mm
Nominal Ø D _c	15 mm

Shank	Plain shank
Series	CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	80 m/min	N
Aluminium (short chipping)	suitable	63 m/min	N
Alu > 10% Si	suitable	50 m/min	N
Steel < 500 N/mm ²	suitable	35 m/min	P
Steel < 750 N/mm ²	suitable	32 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	20 m/min	P
GG(G)	suitable	30 m/min	K
CuZn	suitable	40 m/min	N
Oil	suitable		
wet maximum	suitable		