

Garant**Pair of gloves MASTER FIT ESD, Glove size: 12****Order data**

Order number	094304 12
GTIN	4062406745677
Item class	01H

Description**Version:**

MASTER FIT fitters gloves. With innovative water-based PU nitrile coating for high precision, flexibility and sense of touch in dry working environments. Finely structured surface on the palm of the hand due to complex finishing process. **Suitable for touch screens**, allowing smartphone and other touch screens to be operated without removing the gloves. Long life due to very high abrasion resistance. DMF-free and Oeko-Tex® certified.

Protects against electrostatic discharges.

Standard:

EN 388, EN ISO 21420

EN 16350

Note:

Gloves which protect against electrostatic discharges do not insulate the hands against electrical voltages. Not suitable for working on live cables or for protection against electric shock - they protect only the product.

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	12
Series	MASTER FIT
Clothing standard	Oeko-Tex Standard 100
Contents	12
Glove characteristics	Suitable for touch screens
Glove characteristics	DMF-free
electrostatic characteristic	EGB/ESD
Application	reusable
EN 388	4131X
Backing material	Lycra® / polyamide
Coating	Nitrile / PU
Application range	All-round
Application range	Precision
Colour	blue / black
Type of product	ESD gloves