



Cable reel, Type: 15



Order data

Order number	081193 15
GTIN	4062406745714
Item class	02A

Description

Version:

Cable reel with **guided automatic draw-in and roll-up, with multiple stop points per revolution**. High-impact enclosed **plastic housing**. Thermal **overload cut-out**, sturdy H07RN-F neoprene cable with connection point.

Easy to mount on the wall or ceiling, with **180° pivoting range**.

Function:

IP24: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided.

Application:

Improved ergonomics by relieving cable tension, and for ensuring tidiness and avoiding the risk of accidents and injuries due to cables lying on the ground.

Note:

For spring return hose reels see No. 080066 to 080079.

Technical description

Power supply	Mains-powered
Rated power unrolled	2000 (16 A) W
Cable class	H07RN-F
Nominal voltage	230 V

Width	175 mm
IP Index of Protection	IP 24
Height	390 mm
Material cable	Neoprene rubber
Mains frequency	50 Hz
Cable structure	3G1.5
Cable length	15 m
Number of sockets	1
Length	429 mm
Type of product	Cable reel