

Individual stainless steel test pin Tolerance class 1, Type: 2



Order data

Order number	483915 2
GTIN	2050002070820
Item class	48A

Description

Version:

Test pin of stainless and acid-resistant material, hardened (58-62 HRC) and tempered. Surface ground and lapped. From \varnothing 1.50 the dimension is marked on the sleeve; from \varnothing 3.00 on the end face. From \varnothing 1.00 mm, one end chamfered.

Note:

When ordering, **please additionally state the desired \varnothing** , e.g. No. 483915 size 5 **10.008**.

Technical description

Gauging pin length	70 mm
Nominal size	1.001 - 2.999 mm
Pitch	0.001 mm
Chamfer	1
Calibration	L5
Standard	DIN 2269
Tolerance class	1
Hardness	58 – 62 HRC
Type of product	Test pin

Services

CalibrationTest pin maximum \varnothing 20	028240 20
--	-----------

DAkKS calibration Test pin maximum \varnothing 20

028260 20