

Individual stainless steel test pin Tolerance class 1, Type: 5



Order data

| | |
|--------------|---------------|
| Order number | 483915 5 |
| GTIN | 2050002070851 |
| Item class | 48A |

Description

Version:

Test pin of stainless and acid-resistant material, hardened (58-62 HRC) and tempered. Surface ground and lapped. From \varnothing 1.50 the dimension is marked on the sleeve; from \varnothing 3.00 on the end face. From \varnothing 1.00 mm, one end chamfered.

Note:

When ordering, **please additionally state the desired \varnothing** , e.g. No. 483915 size 5 **10.008**.

Technical description

| | |
|--------------------|--------------------|
| Gauging pin length | 70 mm |
| Pitch | 0.001 mm |
| Nominal size | 10.001 - 11.999 mm |
| Chamfer | 1 |
| Calibration | L5 |
| Standard | DIN 2269 |
| Tolerance class | 1 |
| Hardness | 58 – 62 HRC |
| Type of product | Test pin |

Services

| | |
|--|-----------|
| CalibrationTest pin maximum \varnothing 20 | 028240 20 |
|--|-----------|

DAkKS calibration Test pin maximum \varnothing 20

028260 20