

Garant
DC.T 11T304, Grade: HB7415-1


Order data

Order number	260359 HB7415-1
GTIN	4062406749644
Item class	21G

Description

DC.T 11T304 HB7415-1 Grade: HB7415-1
 Chip breaker: TIS
 Tolerance: M
 Cutting depth a_p : 0.2 - 1.5 mm
 Feed f : 0.05 - 0.3 mm/rev.
 Cutting speed v_c main application: 50 - 110 m/min

Technical description

Number of changes/inserts	2
Chip breaker	TIS
Cutting conditions	continuous
Tolerance	M
ISO code indexable insert	DCMT 11T304
Cutting depth a_p	0.2 - 1.5 mm
Finishing/roughing assignment	Finishing

Grade	HB7415-1
Cutting speed v_c main application	50 - 110 m/min
Corner radius	0.4 mm
Tool material	Carbide
Main application	S
Feed f	0.05 - 0.3 mm/rev.
Type of product	Indexable insert for turning