

Garant**DC.T 11T308, Grade: HB7415-1**

Order data

Order number	260361 HB7415-1
GTIN	4062406749651
Item class	21G

Description

DC.T 11T308 HB7415-1 Grade: HB7415-1
Chip breaker: TIS
Tolerance: M
Cutting depth a_p : 0.2 - 1.5 mm
Feed f : 0.05 - 0.3 mm/rev.
Cutting speed v_c main application: 50 - 110 m/min

Technical description

Tolerance	M
Cutting conditions	continuous
Tool material	Carbide
Number of changes/inserts	2
Corner radius	0.8 mm
Grade	HB7415-1
Feed f	0.05 - 0.3 mm/rev.

Chip breaker	TIS
Cutting speed v_c main application	50 - 110 m/min
Finishing/roughing assignment	Finishing
Main application	S
Cutting depth a_p	0.2 - 1.5 mm
ISO code indexable insert	DCMT 11T308
Type of product	Indexable insert for turning