

Garant**VBMT 160404, Grade: HB7130-2**

Order data

Order number	261152 HB7130-2
GTIN	4062406750398
Item class	21G

Description

VBMT 160404 HB7130-2 Grade: HB7130-2
Chip breaker: VS
Cutting depth a_p : 0.2 - 1.5 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 80 - 270 m/min

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Cutting speed v_c main application	80 - 270 m/min
Cutting conditions	slightly interrupted
Main application	M
Number of changes/inserts	2
Tool material	Carbide
Finishing/roughing assignment	Finishing

Chip breaker	VS
Feed f	0.1 - 0.3 mm/rev.
ISO code indexable insert	VBMT 160404
Corner radius	0.4 mm
Grade	HB7130-2
Type of product	Indexable insert for turning