

**Compact angle grinder, Type: 7222806****Order data**

Order number	077111 7222806
GTIN	4014586895000
Item class	03F

Description**Version:**

FEIN – Compact angle grinder Ø 125 mm.

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

Supplied with:

Handle, safety guard, clamping nut, wrench.

Manufacturer's designation: CG13-125V

Power consumption: 1300 W

maximum speed: 11500 min⁻¹

Speed range: 2800 - 11500 min⁻¹

maximum disc Ø: 125 mm

maximum cutting depth: 35 mm

Technical description

Weight	2.3 kg
maximum disc Ø	125 mm
Power consumption	1300 W
AC supply voltage	240 V
Speed range	2800 - 11500 min ⁻¹
Mains frequency	50 Hz
maximum vibration to EN	6 m/s ²
Power supply	Mains-powered
Manufacturer's designation	CG13-125V
maximum cutting depth	35 mm
Special features	Electronic speed control
Restart block	yes
maximum speed	11500 min ⁻¹
Type of product	Angle grinder