



Compact angle grinder, Type: 7222826



Order data

| | |
|--------------|----------------|
| Order number | 077111 7222826 |
| GTIN | 4014586895024 |
| Item class | 03F |

Description

Version:

FEIN – Compact angle grinder Ø 125 mm.

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

Supplied with:

Handle, safety guard, clamping nut, wrench.

Manufacturer's designation: CG17-125INOX

Power consumption: 1700 W

maximum speed: 7500 min⁻¹

Speed range: 2200 - 7500 min⁻¹

maximum disc Ø: 125 mm

maximum cutting depth: 35 mm

Technical description

| | |
|----------------------------|-------------------------------|
| maximum cutting depth | 35 mm |
| Restart block | yes |
| Power consumption | 1700 W |
| maximum disc Ø | 125 mm |
| maximum speed | 7500 min ⁻¹ |
| Manufacturer's designation | CG17-125INOX |
| Weight | 2.4 kg |
| AC supply voltage | 240 V |
| maximum vibration to EN | 5 m/s ² |
| Special features | Electronic speed control |
| Power supply | Mains-powered |
| Speed range | 2200 - 7500 min ⁻¹ |
| Mains frequency | 50 Hz |
| Type of product | Angle grinder |