



## Compact angle grinder, Type: 7222796



### Order data

Order number	077111 7222796
GTIN	4014586894980
Item class	03F

### Description

#### Version:

**FEIN – Compact angle grinder Ø 125 mm.**

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

#### Supplied with:

Handle, safety guard, clamping nut, wrench.

Manufacturer's designation: CG10-125

Power consumption: 1000 W

maximum speed: 11000 min<sup>-1</sup>

maximum disc Ø: 125 mm

maximum cutting depth: 35 mm

Weight: 2.1 kg

### Technical description

Restart block	yes
maximum cutting depth	35 mm
Weight	2.1 kg
Power consumption	1000 W
Mains frequency	50 Hz
Special features	short body
maximum speed	11000 min <sup>-1</sup>
AC supply voltage	240 V
maximum vibration to EN	8.5 m/s <sup>2</sup>
maximum disc Ø	125 mm
Power supply	Mains-powered
Manufacturer's designation	CG10-125
Type of product	Angle grinder