



Pneumatic impact wrench 3/8 inch – 1/2 inch, Type: 7748



Order data

Order number	079202 7748
GTIN	015451780722
Item class	03R

Description

Version:

Robust impact wrench with **convenient one-hand changeover using Side-2-Side technology**, composite casing with thermal insulation properties and robust double hammer impact drive. Balanced weight distribution for more comfortable working. Exhaust air is directed downwards through the handle. **Tightening power can be regulated in steps.**

Technical description

Length	175 mm
Operating noise	94.3 dB(A)
Maximum screw Ø (8.8 - 12.9)	M24
maximum speed	7000 min ⁻¹
Connection thread	NPT
Weight	2 kg
maximum vibration to EN	12 m/s ²

Tool arbor drive profile	Square
Tool arbor size	1/2 in
recommended hose size (internal Ø)	10 mm
Compressed air connection	1/4 in
maximum air consumption	180 l/min
Torque range	95 - 750 Nm
Reversible	yes
Type of product	Screwdriver