

**Pneumatic straight die grinder collet Ø 6 mm short, Type: 7405****Order data**

Order number	079456 7405
GTIN	015451781507
Item class	03R

**Description****Version:**

Mini die grinder with high no-load speed for quiet and efficient grinding. Precise power and control due to integrated speed controller.

**Supplied with:**

Supplied with 1 each of 1/4 inch and 6 mm collet.

**Technical description**

Weight	0.5 kg
maximum vibration to EN	3.6 m/s <sup>2</sup>
Compressed air connection	1/4 in
maximum air consumption	78 l/min
Length	200 mm
recommended hose size (internal Ø)	10 mm
Collet Ø	6 mm
Connection thread	NPT
Output power	250 W
Operating noise	76.2 dB(A)

maximum speed	28000 min <sup>-1</sup>
Power supply	Pneumatic
Type of product	Straight die grinder