

ELTEN**Shoe, grey VINTAGE Low ESD, S3, EU shoe size: 37****Order data**

Order number	092230 37
GTIN	4030839220313
Item class	09P

Description**Version:**

Modern safety shoes in vintage design.

- **Upper material of sturdy cowhide.**
- **Breathable textile lining, BIOACTIVE for a pleasant foot climate.**
- **Padded tongue.**
- **ESD PRO grey full-size insole.**
- **L10 TPU/PU sole, anti-slip.**
- **ESD security.**

Safety shoe with bioactive inner lining. Particularly **gentle to the skin and odour-suppressant**.
Extra laces supplied (grey).

Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Supplied with:

With extra laces in grey.

Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 37 – 48.

Technical description

Energy absorption in the heel area	yes
------------------------------------	-----

EU shoe size	37
Material inner lining	breathable textile inner lining
against water penetration and water absorption	yes
Uppers material	Genuine leather
Shoe type	Low shoe
oil- and petrol-resistant sole	yes
Slip resistance	yes
Colour	grey
Puncture resistance	Textile
anti-static	yes
Material of protective toe-cap	Steel
suitable for orthopaedic insoles	yes
The entire shoe is waterproof	yes
Protection class	S3
Material of outer sole	TPU-/PU
Closure	Laces
Standard	Inlay type-tested according to DGUV regulation 191
Series	VINTAGE
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes