

uvex

Lace-up boot, black/yellow uvex 1, S2, EU shoe size: 48



Order data

Order number	092118 48
GTIN	4031101534909
Item class	04V

Description

Version:

Sporty, especially lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.

- **Micro-velour uppers.**
- **Distance Mesh lining material.**
- **100% metal-free uvex xenova® toecap.**
- **PU sole with TPU inserts with the best damping characteristics.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Lace-up boot with soft padded collar and padded tongue.

Standard:

EN ISO 20345:2011 S2 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

electrostatic characteristic: EGB/ESD

Protection class: S2

Material of protective toe-cap: Composite

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

against water penetration and water absorption	yes
--	-----

The entire shoe is waterproof	yes
suitable for those with chrome allergy.	yes
Material of protective toe-cap	Composite
Material inner lining	Distance Mesh
Uppers material	Hydrophobic high-tech micro-velour
contains no metal or leather	yes
EU shoe size	48
Slip resistance	yes
Shoe type	Bootlaces
oil- and petrol-resistant sole	yes
Closure	Laces
Colour	black / yellow
Standard	Inlay type-tested according to DGUV regulation 191
anti-static	yes
Energy absorption in the heel area	yes
Material of outer sole	Polyurethane
removable footbed	yes
Protection class	S2
Series	uvex 1
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety boots