



## Core LED torch with batteries, Type: P4-CORE



### Order data

Order number	081370 P4-CORE
GTIN	4058205028493
Item class	04B

### Description

#### Version:

Ledlenser is one of the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head.

Core series Ledlenser, the new generation of the well-known P series. **Advanced Focus System (AFS)**

The Advanced Focus System is a combination of lens and reflector, thus incorporating the advantages of both systems. The result is an outstanding concentration of light in focus, together with a largely homogeneous unfocussed light beam. This makes the AFS one of the best focussing systems in the world for LED lamps.

#### Rapid Focus

Conventional focussing systems with twist knobs must be operated manually with both hands. Rapid Focus, on the other hand, allows quick adjustment of the light beam with only one hand.

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

Including batteries.

### Technical description

Illumination time stage 2	9 h
Bulb	LED module
Illumination step 2	60 lm

Power supply	Battery-powered
Number of batteries contained	2
Illumination	120 lm
Battery type	Micro, AAA
Manufacturer's designation	P4 Core
Overall length	150 mm
Weight	58 g
IP Index of Protection	IP 54
Illumination time	5 h
Illumination step 3	15 lm
Torch function	Focus
Head Ø	15 mm
Rapid Focus	yes
Advanced Focus System (AFS)	yes
Illumination time stage 3	20 h
Type of product	Flashlight