



Core LED torch with rechargeable battery, Type: P4R-CORE



Order data

| | |
|--------------|-----------------|
| Order number | 081468 P4R-CORE |
| GTIN | 4058205020398 |
| Item class | 04B |

Description

Version:

LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head. Core series Ledlenser, the new generation of the well-known P series.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with USB charging cable.

Technical description

| | |
|------------------------------|------------------------------|
| Head Ø | 15 mm |
| Illumination | 200 lm |
| Power supply | Rechargeable battery-powered |
| Type of rechargeable battery | Lithium-ion |
| Overall length | 150 mm |
| IP Index of Protection | IP 54 |
| Illumination step 2 | 90 lm |
| Illumination step 3 | 15 lm |
| Illumination time stage 2 | 3 h |

| | |
|--|------------|
| Weight | 55 g |
| Number of rechargeable batteries contained | 1 |
| Illumination time stage 3 | 25 h |
| Illumination time | 1.5 h |
| Type of product | Flashlight |